


**VICOR CONFIDENTIAL**

THIS DOCUMENT AND THE DATA DISCLOSED HEREIN OR HERewith IS NOT TO BE REPRODUCED, USED, OR DISCLOSED IN WHOLE OR IN PART TO ANYONE WITHOUT PERMISSION OF VICOR CORP.

REV.	DESCRIPTION	DATE	APPROVED
1	RELEASED PER E071481	JS 07/17/07	REJH



**NOTES:**

1. MAKE FROM VICOR P/N 29804
2. FINISH: ELECTROLESS NICKEL PLATE PER ASTM B607-91. THICKNESS .000120" TO .000300" (3 TO 8 μM).
3. REMOVE ALL BURRS AND SHARP EDGES
4. "⊕" DENOTES CRITICAL CHARACTERISTIC FOR LOT INSPECTION
5. RoHS COMPLIANT, LEAD FREE PER CST-0001 LATEST REVISION

DRAWN BY <i>D.CVINAR</i>		DATE <i>06/05</i>			
<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE MM (INCH) TOLERANCES ARE:</small> <small>DECIMALS</small> <small>ANGLES</small> X.XX+0.25 [0.01]      ±1° X.XXX+0.127 [0.005]					
THIRD ANGLE PROJECTION		SIZE <b>B</b>	FSCM NO. <b>67131</b>	DWG NO <b>30382</b>	REV <b>1</b>
DO NOT SCALE DRAWING		SCALE 2:1	SHEET 1 OF 1		

**HEATSINK  
HALF VIC LF 6.3MM HIGH**