


REV.	DESCRIPTION	DATE	APVD
SEE SHEET 1			

CONFIGURATION 'H'

SINGLE OUTPUT
WITH PLUGMATES




CUSTOMER MUST WIRE OUTPUTS OF CONVERTERS IN PARALLEL AS SHOWN REFER TO DATA SHEET FOR DETAILS

TOLERANCES: .XX = .02
MM .5

.XXX = .010
MM .25

CONFIGURATION 'H'

DUAL OUTPUT
WITH PLUGMATES



TOLERANCES: .XX = .02
MM .5


.XXX = .010
MM .25

DRAWN BY A. ARDMAN	DATE 6/11/02			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES .XX .XX .XX .XX .XX .XX				
THIRD ANGLE PROJECTION	SIZE D	PSCH NO. 67131	DWG NO. 25336	REV 2
DO NOT SCALE DRAWING	SCALE 1:1	SHEET 2 OF 2		

REV.	DESCRIPTION	DATE	APVD
1	RELEASED PER E0430434	PEI 09/20/04	FN
2	REVSD PER E0530903	AK 07/19/05	FN

CONFIGURATION 'H'


SINGLE OUTPUT
WITH LUGMATES



TOLERANCES: .XX = .02 .XXX = .010
MM .5 MM .25

CONFIGURATION 'H'

DUAL OUTPUT
WITH LUGMATES



TOLERANCES: .XX = .02 .XXX = .010
MM .5 MM .25

DRAWN BY A. ARDMAN	DATE 6/11/02			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES .XX .XX .XX .XX .XX .XX				
THIRD ANGLE PROJECTION	SIZE D	PSCH NO. 67131	DWG NO. 25336	REV 2
DO NOT SCALE DRAWING	SCALE 1:1	SHEET 1 OF 2		

OUTLINE DRAWING
VIPAC ARRAY CONFIG "H"